



Tyvek®

SCIENCE
THAT PROTECTS

500 Xpert

MODEL CHF5

Cat. III

 PROTECTION LEVEL

12 | XXXX | 2

1 | **Tyvek®** model CHF5 | 3

13 | 500 | 4

10 | Xpert | 4

13 |  | 5

10 |  Protective Clothing Category III | 5

14 |  TYPE 5-B | 8

2 | EN ISO 13982-1:2004 | 8

7 | +A1:2010 | 8

11 | TYPE 6-B | 8

9 | EN 13034:2005+A1:2009 | 8

15 | EN 1149-5: 2008 | 8

2 | EN 14126: 2003 | 8

7 |  | 8

11 |  | 8

9 | EN 1073-2:2002 | 6

15 | Class 2 | 6

..... Other certification(s) independent of CE marking |

..... Уровень Защиты K50, Ц150, Пм, Вн |

..... модель CHF5 |

..... Комбинезон |

..... EAC |

..... TP TC 019/2011 |

.....  |

..... Ref.: XXX XXX |


..... Made in XXX |

..... Произведено в XXX |

.....  |

..... DuPont de Nemours (Luxembourg) s.à r.l |

..... L-2984 Luxembourg |

.....  |

..... cm |

..... cm |

.....  |

.....  |

.....  |

.....  |

.....  |

.....  |

.....  |

.....  |

.....  |

.....  |

EN • Instructions for Use

Copyright © 2018 DuPont. All rights reserved. The DuPont Oval Logo, DuPont™, Tyvek® and all products denoted with ® or ™ are registered trademarks or trademarks of E. I. du Pont de Nemours and Company or its affiliates.

Internet: www.ipp.dupont.com


DuPont de Nemours (Luxembourg) s.à r.l

L-2984 Luxembourg

CE Ref.: Tyvek® 500 Xpert model CHF5

April 2018/1/V2

DuPont Ref.: IFUTV5XP_010

BODY MEASUREMENTS CM


| Size | Chest girth | Body height |
|------|-------------|-------------|
| S | 84 - 92 | 162 - 170 |
| M | 92 - 100 | 168 - 176 |
| L | 100 - 108 | 174 - 182 |
| XL | 108 - 116 | 180 - 188 |
| 2XL | 116 - 124 | 186 - 194 |
| 3XL | 124 - 132 | 192 - 200 |

THE FIVE CARE PICTOGRAMS INDICATE

| | |
|--|---|
| | Do not wash. Laundering impacts upon protective performance (e. g. antistat will be washed off). • Nicht waschen. Waschen hat Auswirkungen auf die Schutzleistung (z.B. ist der Schutz gegen statische Aufladung nicht mehr gewährleistet). • Ne pas laver. Le nettoyage à l'eau altère les performances de protection (le traitement antistatique disparaît au lavage, par ex.). • Non lavare. Il lavaggio danneggia le caratteristiche protettive (eliminando, ad esempio, il trattamento antistatico). • No lavar: el lavado afecta a la capacidad de protección (p.ej. pérdida del revestimiento antiestático). • Não lavar. A lavagem produzirá impactos no desempenho da protecção (ex.: o efeito anti-estático desaparecerá). • Não lavar. A lavagem produzirá impactos no desempenho da protecção (ex.: o efeito anti-estático desaparecerá). • Tåler ikke vask. Vask påvirker beskyttelseegenskaper (f. eks. vil den antistatiske beskyttelsen vaskes bort.). • Må ikke vaskes. Tørvask påvirker de beskyttende egenskaber (f. eks. vil den antistatiske behandling blive vasket af). • Får ej tvättas. Tvättning påverkar skyddsförmågan (antistatbehandlingen tvättas bort). • Ei saa pestä. Peseminen vaikuttaa suojaustehoön (mm. antistaattisuusaine poistuu pesussa). • Nie prać. Pranie pogarsza właściwości ochronne (np. środek antystatyczny zostanie usunięty podczas prania). • Ne mossa. A mosás hatással van a ruha védőképeségére (pl. az antizstatikus réteg lemosódik). • Neprat. Prání má dopad na ochranné vlastnosti oděvu (např. smývání antistatické vrstvy). • He peri. Машинното пране въздейства върху защитното действие (например антистатикът ще се откъсне). • Neprat. Pranie má vplyv na ochranné vlastnosti oděvu (napr. zmyvávanie antistatickej vrstvy). • Ne prati. Pranje in likanje negativno učinkujeta na varovalne lastnosti (npr. zaščita pred elektrostaticnim nabojem se spere). • Nu spălați. Spălarea afectează calitățile de protecție (de ex. protecția contra electricității statice dispare). • He стирать. Стирка влияет на защитные характеристики (например, смывается антистатический состав). • Neskaltbi. Skalbimas kenkia arsaugai (pvz., nusiplauna antistatinė arsauga). • Nemazgāt. Mazgāšana var ietekmēt tērpa aizsargfunkcijas. (piem. var nomazgāt antistata pārklājumu). • Mitte pesta. Pesemine mõjutab kaitseomadusi (nt antistaatik võidakse välja pesta). • Υικαμαγιν. Υικαμα, koruma performansini etkiler (örneğin antistatik özelliik kaybolur). • Μην πλένετε τη φόρμα. Το πλύσιμο επηρεάζει την παρεχόμενη προστασία (π.χ. η φόρμα θα χάσει τις αντιστατικές της ιδιότητες). |
| | Do not iron. • Nicht bügeln. • Ne pas repasser. • Non stirare. • Non planchar. • Não passar a ferro. • Niet strijken. • Skal ikke strykes. • Må ikke stryges. • Får ej strykas. • Ei saa sillittää. • Nie prasować. • Nežehliti. • He gliadi. • Nežehliti. • Ne likati. • Nu călcați cu fierul de călcat. • He гладить. • Nelyginti. • Negludinat. • Mitte triikida. • Ütlemeysin. • Απαγορεύεται το σιδερώωμα. |
| | Do not machine dry. • Nicht im Wäschetrockner trocknen. • Ne pas sécher en machine. • Non asciugare nell'asciugatrice. • No usar secadora. • Não colocar na máquina de secar. • Niet machinaal drogen. • Må ikke tørkes i trommel. • Må ikke tørretumbles. • Får ej tortkumläs. • Ei saa kuivatata koneellisesti. • Nie suszyć w suszarnie. • Ne szárítsa géppel. • Nesušit v sušičke. • He суши машинно. • Nesušit v sušičke. • Ne sušiti v stroju • Nu puneți în mașina de uscat rufe. • He подвергать машинной стирке. • Nedžiovinti džiovnykėje. • Neveikt automātisko žāvēšanu. • Ärge masinkuivatage. • Kurutma makinesinde kurutmayın. • Απαγορεύεται η χρήση στεγνωτηρίου. |
| | Do not dry clean. • Nicht chemisch reinigen. • Ne pas nettoyer à sec. • Non lavare a secco. • No limpiar en seco. • Não limpar a seco. • Niet chemisch reinigen. • Må ikke renses. • Må ikke kemisk renses. • Får ej kemtvättas. • Ei saa puhdistaa kemiallisesti. • Nie czyścić chemicznie. • Ne tisztítsa vegyileg. • Nečistit chemicky. • He почиствай чрез химическо чистене. • Nečistiť chemicky. • Ne kemično čistiti. • Nu curățați chimic. • He подвергать химической чистке. • Nevalyti cheminiu būdu. • Neveikt ķīmisko tīrīšanu. • Ärge piüüdke puhastada. • Kuru temizleme yapmayın. • Απαγορεύεται το στεγνό καθάρισμα. |
| | Do not bleach. • Nicht bleichen. • Ne pas utiliser de javel. • Non candeggiare. • No usar lejía. • Não usar lixívia. • Niet bleken. • Må ikke blekes. • Må ikke bleges. • Får ej blekas. • Ei saa valkaista. • Nie wybielać. • Ne fehéritse. • Nebélit. • He избелвай. • Nepoužívat bielidlo. • Ne beliti. • Nu folosiți înălbitori. • He отбеливать. • Nebalinti. • Nebalināt. • Ärge valgendage. • Çamaşır suyu kullanmayın. • Απαγορεύεται η χρήση λευκαντικού. |

ENGLISH
INSTRUCTIONS FOR USE

INSIDE LABEL MARKINGS ① Trademark. ② Overall manufacturer. ③ Model identification - Tyvek® 500 Xpert model CHFS is the model name for a hooded protective coverall with cuff, ankle, facial and waist elastication. This instruction for use provides information on this coverall. ④ CE marking - Coverall complies with requirements for category III personal protective equipment according to European legislation, Regulation (EU) 2016/425. Type-examination and quality assurance certificates were issued by SGS United Kingdom Ltd., Weston-super-Mare, BS22 6WA, UK, identified by the EC Notified Body number 0120. ⑤ Indicates compliance with European standards for chemical protective clothing. ⑥ Protection against particulate radioactive contamination according to EN 1073-2:2002. ⚠ EN 1073-2 clause 4.2. requires resistance to ignition. However resistance to ignition was not tested on this coverall. ⑦ This coverall is antistatically treated and offers electrostatic protection according to EN 1149-1:2006 including EN 1149-5:2008 when properly grounded. ⑧ Full-body protection "types" achieved by this coverall defined by the European standards for chemical protective clothing: EN ISO 13982-1:2004 + A1:2010 (Type 5) and EN 13034:2005 + A1:2009 (Type 6). This coverall also fulfills the requirements of EN 14126:2003 Type 5-B and Type 6-B. ⑨ Wearer should read these instructions for use. ⑩ Sizing pictogram indicates body measurements (cm) & correlation to letter code. Check your body measurements and select the correct size. ⑪ Country of origin. ⑫ Date of manufacture. ⑬ Flammable material. Keep away from fire. This garment and/or fabric are not flame resistant and should not be used around heat, open flame, sparks or in potentially flammable environments. ⑭ Do not re-use. ⑮ Other certification(s) information independent of the CE marking and the European notified body.

PERFORMANCE OF THIS COVERALL:
FABRIC PHYSICAL PROPERTIES

| Test | Test method | Result | EN Class* |
|--------------------------------|---------------------------------|---|-----------|
| Abrasion resistance | EN 530 Method 2 | > 100 cycles | 2/6*** |
| Flex cracking resistance | EN ISO 7854 Method B | > 100 000 cycles | 6/6*** |
| Trapezoidal tear resistance | EN ISO 9073-4 | > 10 N | 1/6 |
| Tensile strength | EN ISO 13934-1 | > 60 N | 2/6 |
| Puncture resistance | EN 863 | > 10 N | 2/6 |
| Surface resistance at RH 25%** | EN 1149-1:2006 • EN 1149-5:2008 | inside and outside ≤ 2,5x10 ¹⁰ Ohm | N/A |

N/A = Not applicable *According to EN 14325:2004 **See limitations of use ***Visual end point

FABRIC RESISTANCE TO PENETRATION BY LIQUIDS (EN ISO 6530)

| Chemical | Penetration index - EN Class* | Repellency index - EN Class* |
|------------------------|-------------------------------|------------------------------|
| Sulphuric acid (30%) | 3/3 | 3/3 |
| Sodium hydroxide (10%) | 3/3 | 3/3 |

* According to EN 14325:2004

FABRIC RESISTANCE TO PERMEATION BY LIQUIDS (EN ISO 6529 METHOD A - BREAKTHROUGH TIME AT 1 µg/cm²/min)

| Chemical | Breakthrough time (min) | EN Class* |
|----------------------|-------------------------|-----------|
| Sulphuric acid (18%) | > 480 | 6/6 |

* According to EN 14325:2004 ⚠ Stitched seams do not offer a barrier to permeation of liquids

FABRIC RESISTANCE TO PENETRATION OF INFECTIVE AGENTS

| Test | Test method | EN Class* |
|---|-----------------------|-------------------|
| Resistance to penetration by blood and body fluids using synthetic blood | ISO 16603 | 3/6 |
| Resistance to penetration by blood-borne pathogens using bacteriophage Phi-X174 | ISO 16604 Procedure C | no classification |
| Resistance to penetration by contaminated liquids | EN ISO 22610 | 1/6 |
| Resistance to penetration by biologically contaminated aerosols | ISO/DIS 22611 | 1/3 |
| Resistance to penetration by biologically contaminated dust | ISO 22612 | 1/3 |

* According to EN 14126:2003

WHOLE SUIT TEST PERFORMANCE

| Test method | Test result | EN Class |
|---|--|-----------|
| Type 5: Particle aerosol inward leakage test (EN ISO 13982-2) | Pass*** • L _{mm} 82/90 ≤ 30% • L _s 8/10 ≤ 15% ** | N/A |
| Protection factor according to EN 1073-2 | > 50 | 2 of 3*** |
| Type 6: Low level spray test (EN ISO 17491-4, Method A) | Pass | N/A |
| Seam strength (EN ISO 13935-2) | > 75 N | 3/6* |

N/A = Not applicable *According to EN 14325:2004 ** 82/90 means 91,1% L_{mm} values ≤ 30% and 8/10 means 80% L_s values ≤ 15%

***Test performed with taped cuffs, hood, ankles and zipper flap

For further information about the barrier performance, please contact your supplier or DuPont: www.ipp.dupont.com

RISKS AGAINST WHICH THE PRODUCT IS DESIGNED TO PROTECT: This coverall is designed to protect workers from hazardous substances, or sensitive products and processes from contamination by people. It is typically used, depending on chemical toxicity and exposure conditions, for protection against fine particles (Type 5) and limited liquid splashes or sprays (Type 6). A full face mask with filter appropriate for the exposure conditions and tightly connected to the hood and additional taping around the hood, cuffs, ankles and zipper flap are required to achieve the claimed protection. Fabric used for this coverall has been tested according to EN 14126:2003 (protective clothing against infective agents) with the conclusion that the material offers a limited barrier against infective agents (see above table).

LIMITATIONS OF USE: This garment and/or fabric are not flame resistant and should not be used around heat, open flame, sparks or in potentially flammable environments. Tyvek® melts at 135°C. It is possible that a type of exposure to bio hazards not corresponding to the tightness level of the garment

may lead to a bio-contamination of the user. Exposure to certain very fine particles, intensive liquid sprays and splashes of hazardous substances may require coveralls of higher mechanical strength and barrier properties than those offered by this coverall. The user must ensure suitable reagent to garment compatibility before use. In addition, the user shall verify the fabric and chemical permeation data for the substance(s) used. Stitched seams of this coverall do not offer barrier to infective agents nor are a barrier to permeation of liquids. For increased protection the wearer should select a garment comprising seams that offer equivalent protection as the fabric (e.g. stitched & overtaped seams). For enhanced protection and to achieve the claimed protection in certain applications, taping of cuffs, ankles, hood and zipper flap will be necessary. The user shall verify that tight taping is possible in case the application would require doing so. Care shall be taken when applying the tape, that no creases appear in the fabric or tape since those could act as channels. When taping the hood, small pieces (+/- 10 cm) of tape should be used and overlap. This garment meets the surface resistance requirements of EN 1149-5:2008 when measured according to EN 1149-1:2006. The antistatic treatment is only effective in a relative humidity of 25% or above and the user shall ensure proper grounding of both the garment and the wearer. The electrostatic dissipative performance of both the suit and the wearer needs to be continuously achieved in such a way as the resistance between the person wearing the electrostatic dissipative protective clothing and the earth shall be less than 10⁹ Ohm e.g. by wearing adequate footwear/flooring system, use of a grounding cable, or by any other suitable means. Electrostatic dissipative protective clothing shall not be opened or removed whilst in presence of flammable or explosive atmospheres or while handling flammable or explosive substances. Electrostatic dissipative protective clothing shall not be used in oxygen enriched atmospheres without prior approval of the responsible safety engineer. The electrostatic dissipative performance of the electrostatic dissipative clothing can be affected by relative humidity, wear and tear, possible contamination and ageing. Electrostatic dissipative protective clothing shall permanently cover all non-complying materials during normal use (including bending and movements). In situations where static dissipation level is a critical performance property, endusers should evaluate the performance of their entire ensemble as worn including outer garments, inner garments, footwear and other PPE. Further information on grounding can be provided by DuPont. Please ensure that you have chosen the garment suitable for your job. For advice, please contact your supplier or DuPont. The user shall perform a risk analysis upon which he shall base his choice of PPE. He shall be the sole judge for the correct combination of full body protective coverall and ancillary equipment (gloves, boots, respiratory protective equipment etc.) and for how long this coverall can be worn on a specific job with respect to its protective performance, wear comfort or heat stress. DuPont shall not accept any responsibility whatsoever for improper use of this coverall.

PREPARING FOR USE: In the unlikely event of defects, do not wear the coverall.

STORAGE AND TRANSPORT: This coverall may be stored between 15 and 25°C in the dark (cardboard box) with no UV light exposure. DuPont has performed naturally and accelerated ageing tests with the conclusion that this fabric retains adequate physical strength and barrier properties over a period of 10 years. The antistatic properties may reduce over time. The user must ensure the dissipative performance is sufficient for the application. Product shall be transported and stored in its original packaging.

DISPOSAL: This coverall can be incinerated or buried in a controlled landfill without harming the environment. Disposal of contaminated garments is regulated by national or local laws.

DECLARATION OF CONFORMITY: Declaration of conformity can be downloaded at: www.safespec.dupont.co.uk.

Additional information for other certification(s) independent of CE marking.

Eurasian Conformity (EAC) - Complies with Technical Regulations of the Customs Union TRTS 019/2011.

Евразийское соответствие (EAC) - Соответствует Техническому регламенту Таможенного союза ТР ТС 019/2011.

Комбинезон

EAC

ТР ТС 019/2011

Уровень Защиты K50,
Щ50, Пм, Вн